

ALPHA STAINLESS

8477UAD100P30-11 RED

EAN 4031582370164



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Alpha stainless
Housing type	Swivel castor with total lock
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	150 kg
Load capacity Static	300 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall height	128 mm
Overall weight	0.957 kg

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Roller bearing, stainless
Axle	Screwed with nut
Diameter	100 mm
Tread width	32 mm
Hardness of tread (D)	42 Shore D

HOUSING

Material fork	Stainless steel, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Offset	41 mm
Swivel interference	242 mm
Stainless	✓

FITTING

Fitting type	Bolt hole
Bolt hole diameter	11 mm

ALPHA STAINLESS

8477UAD100P30-11 RED

EAN 4031582370164



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

