

AGILA TWIN

2970PJP075P50 offset-31,4 axle-M8

EAN 4031582302738



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ● ○

CORE ATTRIBUTES

Product Name	Agila twin
Type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Electric Conductive	No
Stainless	No
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	102 mm
Overall width	71 mm
Overall weight	0.63 kg

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Twin wheel housing
Swivel Bearing	Two ball races
Housing Color	Blue passivated
Offset	31.4 mm
Swivel radius	72.5 mm
Swivel interference	145 mm
Dome diameter	65 mm

WHEEL

Body material	Polypropylene
Tread Material Mix	Thermoplastic rubber
Bearing	Precision ball bearing
Wheel Color	Silver grey (RAL7001)
Threadguards	With threadguard
Diameter	75 mm
Tread width	25 mm
Body width	25 mm
Hardness of tread (A)	87 Shore A

FITTING

Fitting type	Rectangular plate
Plate length	77 mm
Plate width	67 mm
Plate hole length (Minimum)	46.5 mm
Plate hole length (Maximum)	51.5 mm
Plate hole width (Minimum)	56 mm
Plate hole width (Maximum)	61.5 mm
Plate hole diameter	8.5 mm

AGILA TWIN

2970PJP075P50 offset-31,4 axle-M8

EAN 4031582302738

Order number 00027436
Product Drawings



BETTER MOBILITY. BETTER LIFE.

