

KAPPA

9688FTP300P65

EAN 4031582316360



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Kappa
Type	Fixed castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	2400 kg
Load capacity at 6 km/h	2000 kg
Electric Conductive	No
Stainless	No
Load capacity Static	4800 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	355 mm
Overall weight	18.34 kg

HOUSING

Housing Material	Iron forged, heavy
Fork shape	Broad, reinforced
Lubrication nipple	1

WHEEL

Body material	Cast iron
Tread Material Mix	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	With threadguard
Diameter	300 mm
Tread width	80 mm
Hardness of tread (A)	92 Shore A

FITTING

Fitting type	Medium rectangular heavy-duty plate
Plate length	200 mm
Plate width	160 mm
Plate hole length (Maximum)	160 mm
Plate hole width (Maximum)	120 mm
Plate hole diameter	15 mm

