

ZETA

4688FTP200P63 TFR

EAN 4031582386295



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Zeta
Type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	800 kg
Load capacity at 6 km/h	640 kg
Electric Conductive	No
Stainless	No
Load capacity Static	1600 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	240 mm
Overall weight	2.65 kg

HOUSING

Housing Material	Steel sheet, very heavy
Fork shape	Broad, reinforced
Housing Color	Blue passivated

WHEEL

Body material	Cast iron
Tread Material Mix	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	With threadguard
Diameter	200 mm
Tread width	50 mm
Hardness of tread (A)	92 Shore A

FITTING

Fitting type	Medium rectangular plate
Plate length	137 mm
Plate width	105 mm
Plate hole length (Maximum)	105 mm
Plate hole width (Minimum)	74 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	11 mm

ZETA

4688FTP200P63 TFR

EAN 4031582386295



BETTER MOBILITY. BETTER LIFE.

Product Drawings

