

ZETA

4688IEP125P63

EAN 4031582308259



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

|                      |             |
|----------------------|-------------|
| Roll Performance     | ● ● ● ● ● ○ |
| Movement noise       | ● ● ● ● ● ● |
| Attrition            | ● ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ○ ○ |

CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Zeta                          |
| Type                        | Fixed caster                  |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph    | 661.39 lb                     |
| Load capacity at 3.7 mph    | 1234.59 lb                    |
| Electric conductive         | no                            |
| Stainless                   | no                            |
| Load capacity Static        | 1322.77 lb                    |
| Temperature range (Minimum) | -4 °F                         |
| Temperature range (Maximum) | 185 °F                        |
| Overall height              | 6.46 in                       |
| Overall width               | 4.61 in                       |
| Overall weight              | 4.12 lb                       |

HOUSING

|                  |                         |
|------------------|-------------------------|
| Housing Material | Steel sheet, very heavy |
| Fork shape       | Broad, reinforced       |
| Housing Color    | Blue passivated         |

WHEEL

|                       |                                 |
|-----------------------|---------------------------------|
| Tread hardness        | soft                            |
| Body material         | Aluminum                        |
| Tread material        | Elastic tire, black, vulcanized |
| Bearing               | Precision ball bearing          |
| Axle                  | Screwed with nut                |
| Wheel color           | Jet black (similar RAL9005)     |
| Threadguards          | Without threadguard             |
| Diameter              | 4.92 in                         |
| Tread width           | 1.97 in                         |
| Body width            | 1.97 in                         |
| Hardness of tread (A) | 67 Shore A                      |

FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 5.39 in           |
| Plate width                 | 4.61 in           |
| Plate hole length (Minimum) | 2.95 in           |
| Plate hole length (Maximum) | 3.15 in           |
| Plate hole width (Minimum)  | 2.95 in           |
| Plate hole width (Maximum)  | 4.13 in           |
| Plate hole diameter         | 0.43 in           |

# ZETA

4688IEP125P63

EAN 4031582308259

Order number 00804232

Product Drawings



BETTER MOBILITY. BETTER LIFE.

