

ZETA

4688IEP125P63

EAN 4031582308259



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ● ○
Movement noise	● ● ● ● ● ●
Attrition	● ● ● ● ○ ○
Corrosion resistance	● ● ● ● ○ ○

CORE ATTRIBUTES

Product name	Zeta
Type	Fixed caster
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	661.39 lb
Load capacity at 3.7 mph	529.11 lb
Electric conductive	no
Stainless	no
Load capacity Static	1322.77 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	185 °F
Overall height	6.46 in
Overall width	4.61 in
Overall weight	4.12 lb

HOUSING

Housing Material	Steel sheet, very heavy
Fork shape	Broad, reinforced
Housing Color	Blue passivated

WHEEL

Tread hardness	soft
Body material	Aluminum
Tread material	Elastic tire, black, vulcanized
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Jet black (similar RAL9005)
Threadguards	Without threadguard
Diameter	4.92 in
Tread width	1.97 in
Body width	1.97 in
Hardness of tread (A)	67 Shore A

FITTING

Fitting type	Rectangular plate
Plate length	5.39 in
Plate width	4.61 in
Plate hole length (Minimum)	2.95 in
Plate hole length (Maximum)	3.15 in
Plate hole width (Minimum)	2.95 in
Plate hole width (Maximum)	4.13 in
Plate hole diameter	0.43 in

ZETA

4688IEP125P63

EAN 4031582308259

Order number 00804232

Product Drawings



BETTER MOBILITY. BETTER LIFE.

