PRODUCT INFORMATION

# LUMINA

A525POI040L51- 8

EAN 4031582443998

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement Noise | ●●●○○ |
| Attrition | ●●●○○ |
| Corrosion Resistance | ●●●○○ |

## CORE ATTRIBUTES

| | |
|---|---|
| Product Name | Lumina |
| Type | Swivel castor with wheel brake |
| Standard | EN12528 - Furniture Castors |
| Load capacity at 3 km/h | 10 kg |
| Electric Conductive | No |
| Stainless | No |
| Load capacity Static | 20 kg |
| Temperature range (Minimum) | -10 °C |
| Temperature range (Maximum) | 40 °C |
| Overall Height | 44 mm |
| Overall width | 38 mm |
| Overall weight | 0.03 kg |

## HOUSING

| | |
|---|---|
| Housing Material | Polypropylene |
| Fork shape | Twin wheel housing, closed, with dome |
| Swivel Bearing | Stem, swiveling |
| Swivel radius | 52 mm |
| Swivel interference | 104 mm |

## WHEEL

| | |
|---|---|
| Body material | Polypropylene |
| Tread Material Mix | Identical with wheel body |
| Bearing | Plain bearing with spacer tube |
| Axle | Riveted |
| Threadguards | Without threadguard |
| Diameter | 40 mm |
| Tread width | 6 mm |
| Hardness of tread (D) | 65 Shore D |

## FITTING

| | |
|---|---|
| Fitting type | Blind hole for B10 |
| Bolt hole diameter | 8 mm |

© Copyright 2026 TENTE International GmbH


# LUMINA

A525POI040L51- 8

EAN 4031582443998

BETTER MOBILITY. BETTER LIFE.

## Product Drawings



© Copyright 2026 TENTE International GmbH