

PURETECH

DIK 075x25-Ø6,1

EAN 4031582070149



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Puretech
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	121.25 lb
Electric conductive	no
Stainless	no
Load capacity Static	242.51 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	185 °F
Overall weight	0.49 lb

WHEEL

Body material	Sheet Steel
Tread material	Solid rubber, non-marking
Bearing	Cone ball bearing
Wheel color	Blue passivated
Threadguards	With threadguard
Diameter	2.95 in
Tread width	0.98 in
Axle hole diameter	0.24 in
Hub length	1.1 in
Body width	0.98 in
Hardness of tread (A)	80 Shore A

PURETECH

DIK 075x25-Ø6,1

EAN 4031582070149

Order number 00004955
Product Drawings



BETTER MOBILITY. BETTER LIFE.

