

# ZETA STAINLESS

8671TOO160P63

EAN 4031582313581  
Order number 00830135



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

## CORE ATTRIBUTES

Product name	Zeta stainless
Type	Swivel castor with directional lock
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	800 kg
Load capacity at 6 km/h	640 kg
Stainless	✓
Load capacity Static	1600 kg
Temperature range (Minimum)	-30 °C
Temperature range (Maximum)	80 °C
Overall height	200 mm
Overall width	96 mm
Overall weight	3.115 kg

## WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Plain bearing
Axle	Screwed with nut
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	160 mm
Tread width	50 mm
Body width	50 mm
Hardness of tread (D)	75 Shore D

## HOUSING

Material fork	Stainless steel, heavy
Fork shape	Broad, reinforced
Swivel bearing	Two ball races
Colour	Stainless steel
Offset	55 mm
Swivel radius	135 mm
Swivel interference	270 mm
Dome diameter	96 mm

## FITTING

Fitting type	Medium rectangular plate
Plate length	137 mm
Plate width	105 mm
Plate hole length (Minimum)	74 mm
Plate hole length (Maximum)	80 mm
Plate hole width (Minimum)	74 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	11 mm

# ZETA STAINLESS

8671TOO160P63

EAN 4031582313581  
Order number 00830135



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

