

BASETECH

POR 100X36-Ø12 HL44,4

EAN 4031582320770
Order number 00030952



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Roller bearing
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	100 mm
Tread width	36 mm
Axle hole diameter	12 mm
Hub length	44.4 mm
Body width	36 mm
Hardness of tread (D)	65 Shore D

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Basetech
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	160 kg
Load capacity Static	320 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.143 kg

PRODUCT INFORMATION

BASETECH

POR 100X36-Ø12 HL44,4

EAN 4031582320770
Order number 00030952



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

