

ALPHA

3478DPR200P63 BLACK

EAN 4031582410792



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ○ ○ ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Alpha
Type	Fixed castor
Load capacity at 3 km/h	75 kg
Load capacity Static	150 kg
Overall height	240 mm
Overall weight	1.718 kg

WHEEL

Body material	Sheet Steel
Tread material	Pneumatic tyre, line profile
Bearing	Roller bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	200 mm
Tread width	50 mm

HOUSING

Material fork	Steel sheet, heavy
Fork shape	Broad

FITTING

Fitting type	Medium rectangular plate
Plate length	137 mm
Plate width	115 mm
Plate hole length (Maximum)	105 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	11 mm

ALPHA

3478DPR200P63 BLACK

EAN 4031582410792



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

