

# STYLEA

5923UOI065B10-11X20/10D27 9011/9011

EAN 4031582335699



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                                       |
|-----------------------------|---------------------------------------|
| Product name                | Stylea                                |
| Type                        | Swivel caster with intermittend brake |
| Load capacity at 1.8 mph    | 110.23 lb                             |
| Electric conductive         | no                                    |
| Stainless                   | no                                    |
| Load capacity Static        | 220.46 lb                             |
| Temperature range (Minimum) | -4 °F                                 |
| Temperature range (Maximum) | 140 °F                                |
| Overall height              | 2.68 in                               |
| Overall width               | 1.69 in                               |
| Overall weight              | 0.3 lb                                |

## HOUSING

|                     |                          |
|---------------------|--------------------------|
| Housing Material    | Polyamide                |
| Fork shape          | Twin wheel housing       |
| Swivel bearing      | Stem, swiveling          |
| Housing Color       | Graphite black (RAL9011) |
| Offset              | 0.98 in                  |
| Swivel radius       | 2.09 in                  |
| Swivel interference | 4.17 in                  |
| Dome diameter       | 1.06 in                  |

## WHEEL

|                       |                                |
|-----------------------|--------------------------------|
| Body material         | Polyamide                      |
| Tread material        | Identical with wheel body      |
| Bearing               | Plain bearing with spacer tube |
| Axle                  | Riveted                        |
| Tread color           | Graphite black (RAL9011)       |
| Wheel color           | Graphite black (RAL9011)       |
| Threadguards          | Without threadguard            |
| Diameter              | 2.56 in                        |
| Tread width           | 0.31 in                        |
| Axle hole diameter    | 0 in                           |
| Hub length            | 0 in                           |
| Body width            | 0.31 in                        |
| Hardness of tread (D) | 65 Shore D                     |

## FITTING

|               |                                  |
|---------------|----------------------------------|
| Fitting type  | Stem with grip ring, with collar |
| Stem diameter | 0.43 in                          |
| Stem length   | 0.79 in                          |

# STYLEA

5923UOI065B10-11X20/10D27 9011/9011

EAN 4031582335699

Order number 00078108

**Product Drawings**



BETTER MOBILITY. BETTER LIFE.

