PRODUCT INFORMATION

DURATECH

MOP 160x50-Ø30

EAN 4031582320046



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●●●
Movement Noise	●●○○○
Attrition	●●●●●
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Duratech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	2700 kg
Load capacity at 6 km/h	2250 kg
Electric Conductive	No
Stainless	No
Load capacity Static	4500 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	1.62 kg

WHEEL

Body material	Polyamide, super heavy
Tread Material Mix	Identical with wheel body
Bearing	Precision ball bearing
Wheel Color	Natural white
Threadguards	Without threadguard
Diameter	160 mm
Tread width	50 mm
Axle Hole Diameter	30 mm
Hub Length	60 mm
Body width	50 mm
Hardness of tread (D)	75 Shore D
Bearing type	6306

© Copyright 2026 TENTE International GmbH


DURATECH

MOP 160x50-Ø30

EAN 4031582320046

Order number 00801261

Product Drawings



© Copyright 2026 TENTE International GmbH

DURATECH

MOP 160x50-Ø30

EAN 4031582320046

Order number 00801261

