

PRODUCT INFORMATION

# ELASTECH

UFR200x46-Ø20 blue TFR

EAN 4031582394542



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

### WHEEL

Tread hardness	soft
Body material	Polyamide
Tread Material Mix	Elastic tire, non-marking, vulcanized
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	200 mm
Tread width	46 mm
Axle Hole Diameter	20 mm
Hub Length	58 mm
Hardness of tread (A)	64 Shore A

### PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion Resistance	● ● ● ○ ○

### CORE ATTRIBUTES

Product Name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	400 kg
Electric Conductive	No
Stainless	No
Load capacity Static	800 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall weight	1.21 kg

# ELASTECH

UFR200x46-Ø20 blue TFR

EAN 4031582394542



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

