

PRODUCT INFORMATION

MAXTECH

PNR260x82-Ø20 HL74 yellow

EAN 4031582438185



BETTER MOBILITY. BETTER LIFE.

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Maxtech
Type	Wheel
Load capacity at 3 km/h	75 kg
Electric Conductive	No
Stainless	No
Load capacity Static	150 kg
Overall weight	1.95 kg

WHEEL

Body material	Polypropylene
Tread Material Mix	Polyurethane, foamed
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	260 mm
Tread width	82 mm
Axle Hole Diameter	20 mm
Hub Length	74 mm

MAXTECH

PNR260x82-Ø20 HL74 yellow

EAN 4031582438185



BETTER MOBILITY. BETTER LIFE.

Product Drawings

