

# ALPHA SMART STAINLESS

8377BOG080P30-13

EAN 4031582494495



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

## CORE ATTRIBUTES

Product name	Alpha smart stainless
Type	Swivel castor with total lock
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	100 kg
Stainless	✓
Load capacity Static	200 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	280 °C
Overall height	108 mm
Overall weight	0.722 kg

## WHEEL

Body material	Plastic thermoset, heat-resistant
Tread material	Identical with wheel body
Bearing	Dry bearing bush
Axle	Screwed with nut
Diameter	80 mm
Tread width	35 mm
Hardness of tread (D)	85 Shore D

## HOUSING

Material fork	Stainless steel, heavy
Fork shape	Slim
Swivel bearing	Two ball races
Offset	44.5 mm
Swivel radius	84.5 mm
Swivel interference	169 mm

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	13 mm