

# BASETECH

POR080X34-Ø12 WHITE

EAN 4031582410372



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

Materijal za telo	polipropilen
materijal omotaca	Identično sa telom Tocak
Nošenje	kotrljajući lezaj
štitnici omotaca	Bez stražara
Prečnik	80 mm
Širina omotac	34 mm
dimenzija rupa osovina	12 mm
dužina glavčine	44,4 mm
Teškoća gazećeg omotac (D)	65 Šor D

## PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Basetech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	125 kg
Statički Nosivost	250 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,102 kg

# BASETECH

POR080X34-Ø12 WHITE

EAN 4031582410372



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

---

