

DURATECH

RK.TOP080X70-Ø47X14

EAN 4031582443103



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|---------------------|
| Body material | Undefined |
| Tread material | Polypropylene, soft |
| Diameter | 80 mm |
| Tread width | 70 mm |
| Ball bearing diameter | 47 mm |
| Ball bearing width | 14 mm |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ● |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|----------|
| Product name | Duratech |
| Housing type | Wheel |
| Load capacity at 3 km/h | 650 kg |
| Load capacity Static | 1300 kg |
| Temperature range (Minimum) | -40 °C |
| Temperature range (Maximum) | 80 °C |
| Overall weight | 0.25 kg |

DURATECH

RK.TOP080X70-Ø47X14

EAN 4031582443103



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

