

ICS

5321PJP125P52

EAN 4031582384635



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement Noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

|                             |                                     |
|-----------------------------|-------------------------------------|
| Product Name                | ICS                                 |
| Type                        | Swivel castor with directional lock |
| Standard                    | EN12530 - Devices Castors           |
| Load capacity at 3 km/h     | 100 kg                              |
| Electric Conductive         | No                                  |
| Stainless                   | No                                  |
| Load capacity Static        | 200 kg                              |
| Temperature range (Minimum) | -10 °C                              |
| Temperature range (Maximum) | 40 °C                               |
| Overall Height              | 166 mm                              |

HOUSING

|                     |                 |
|---------------------|-----------------|
| Housing Material    | Polyamide       |
| Fork shape          | Slim            |
| Swivel Bearing      | Stem, swiveling |
| Offset              | 37 mm           |
| Swivel interference | 199 mm          |

WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Polypropylene          |
| Tread Material Mix    | Thermoplastic rubber   |
| Bearing               | Precision ball bearing |
| Threadguards          | Integrated threadguard |
| Diameter              | 125 mm                 |
| Tread width           | 32 mm                  |
| Hardness of tread (A) | 87 Shore A             |

FITTING

|                             |                                         |
|-----------------------------|-----------------------------------------|
| Fitting type                | Rectangular plate, US-bolt hole spacing |
| Plate length                | 95 mm                                   |
| Plate width                 | 70 mm                                   |
| Plate hole length (Minimum) | 44.45 mm                                |
| Plate hole length (Maximum) | 52 mm                                   |
| Plate hole width (Minimum)  | 72 mm                                   |
| Plate hole width (Maximum)  | 76 mm                                   |
| Plate hole diameter         | 11 mm                                   |



# ICS



5321PJP125P52

EAN 4031582384635



BETTER MOBILITY. BETTER LIFE.

## Product Drawings



IF Design  
Award