

MAXTECH

UAR100X36H45

EAN 4031582426953



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

FITTING

Bolt diameter	0.31 in
Bolt length	2.56 in

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Housing type	Wheel
Load capacity at 1.8 mph	440.92 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	-7312 °F
Overall weight	0.73 lb

WHEEL

Diameter	3.94 in
Tread width	1.42 in
Axle hole diameter	0.47 in
Hub length	1.77 in
Bearing type	Roller Bea