

# MOUNTING PLATE

P10-40X19 / 10 TFR

EAN 4031582393880



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Corrosion resistance ●●●○○

## CORE ATTRIBUTES

Product name	Mounting plate
Type	Accessory
Load capacity at 1.8 mph	88.18 lb
Load capacity Static	176.37 lb
Overall height	0.39 in
Overall weight	0.06 lb

## FITTING

Fitting type	Stem with U-shaped plate
Plate length	1.57 in
Plate width	0.75 in
Plate hole length (Maximum)	1.26 in
Plate hole width (Maximum)	1.26 in
Plate hole diameter	0.16 in