

MAXTECH

PNR400X90-Ø10X129 GEEL

EAN 4031582202373



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ○ ○ ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Type	Wheel
Load capacity at 3 km/h	145 kg
Load capacity Static	290 kg
Overall weight	3 kg

WHEEL

Body material	Polypropylene
Tread hardness	soft
Tread material	Polyurethane, foamed
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	400 mm
Tread width	90 mm
Axle hole diameter	10 mm
Hub length	129 mm
Hardness of tread (A)	55 Shore A

MAXTECH

PNR400X90-Ø10X129 GEEL

EAN 4031582202373



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

