

# MAXTECH

PNR260X75-Ø20 HL74 TFR

EAN 4031582400328



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

|                    |                      |
|--------------------|----------------------|
| Body material      | Polypropylene        |
| Tread material     | Polyurethane, foamed |
| Bearing            | Roller bearing       |
| Threadguards       | Without threadguard  |
| Diameter           | 260 mm               |
| Tread width        | 75 mm                |
| Axle hole diameter | 20 mm                |
| Hub length         | 74 mm                |

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                         |         |
|-------------------------|---------|
| Product name            | Maxtech |
| Housing type            | Wheel   |
| Load capacity at 3 km/h | 75 kg   |
| Load capacity Static    | 150 kg  |
| Overall weight          | 1.95 kg |

# MAXTECH

PNR260X75-Ø20 HL74 TFR

EAN 4031582400328



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

