PRODUCT INFORMATION

# ELASTECH

## UFR 125x40-Ø12

EAN 4031582324662

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

### WHEEL

| | |
|---|---|
| Tread hardness | soft |
| Body material | Polyamide |
| Tread Material Mix | Elastic tire, non-marking, vulcanized |
| Bearing | Roller bearing |
| Wheel Color | Silver grey (RAL7001) |
| Threadguards | Without threadguard |
| Diameter | 125 mm |
| Tread width | 40 mm |
| Axle Hole Diameter | 12 mm |
| Hub Length | 44.2 mm |
| Body width | 40 mm |
| Hardness of tread (A) | 63 Shore A |

### PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●●○ |
| Movement Noise | ●●●●○ |
| Attrition | ●●●○○ |
| Corrosion Resistance | ●●●○○ |

### CORE ATTRIBUTES

| | |
|---|---|
| Product Name | Elastech |
| Type | Wheel |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 250 kg |
| Electric Conductive | No |
| Stainless | No |
| Load capacity Static | 500 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 80 °C |
| Overall weight | 0.42 kg |

© Copyright 2026 TENTE International GmbH


# ELASTECH

## UFR 125x40-Ø12

EAN 4031582324662

Order number 00031363

**Product Drawings**




© Copyright 2026 TENTE International GmbH