PRODUCT INFORMATION

MONO

5025PJH080L51-10 RAL7035 regular brake

EAN 4031582460599



Image may differ from the original product

CORE ATTRIBUTES

Product name	Mono
Type	Swivel caster with wheel brake
Load capacity at 1.8 mph	154.32 lb
Electric conductive	no
Stainless	no
Load capacity Static	308.65 lb
Overall height	4.09 in
Overall weight	0 lb

HOUSING

Housing Material	Polyamide
Fork shape	Closed
Swivel bearing	Stem, swiveling
Housing Color	Light gray (RAL7035)
Offset	1.34 in
Swivel interference	5.83 in

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Threadguards	With threadguard
Diameter	3.15 in
Tread width	0.94 in
Hardness of tread (A)	87 Shore A

FITTING

Fitting type	Blind hole for B10 fitting
Bolt hole diameter	0.39 in

© Copyright 2026 TENTE International GmbH


MONO

5025PJH080L51-10 RAL7035 regular brake

EAN 4031582460599

BETTER MOBILITY. BETTER LIFE.

Product Drawings



© Copyright 2026 TENTE International GmbH