

SCOUT

814SUF200P60 180° SMART

EAN 4031582429916



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	●●●○○
Movement noise	●●●●●
Attrition	●●●○○
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Scout
Type	Swivel castor with spring loaded directional lock
Load capacity at 1.8 mph	330.69 lb
Load capacity at 2.5 mph	330.69 lb
Stainless	✓
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	176 °F
Overall height	9.53 in
Overall width	2.83 in
Overall weight	6.42 lb

WHEEL

Body material	Polyamide
	soft
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing, stainless
Threadguards	With threadguard
Diameter	7.87 in
Tread width	1.57 in
Hardness of tread (A)	64 Shore A

HOUSING

Material	Stainless steel, heavy
Fork shape	Angular
Swivel bearing	Precision ball bearing
Offset	1.97 in
Swivel radius	5.91 in
Swivel interference	11.81 in

FITTING

Fitting type	Rectangular plate
Plate length	5.12 in
Plate width	2.91 in
Plate hole length (Maximum)	4.33 in
Plate hole width (Maximum)	1.97 in
Plate hole diameter	0.41 in

SCOUT

814SUFC200P60 180° SMART

EAN 4031582429916



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

