

COMPACTA

1430POI050P60-59X47 (24)

EAN 4031582332513



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Compacta
Housing type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	40 kg
Load capacity Static	80 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	66 mm
Overall weight	0.143 kg

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	50 mm
Tread width	21 mm
Hardness of tread (D)	65 Shore D

HOUSING

Material fork	Steel sheet, light
Fork shape	Broad
Swivel bearing	One ball race
Offset	16 mm
Swivel radius	41 mm
Swivel interference	82 mm

FITTING

Fitting type	Rectangular plate
Plate length	59 mm
Plate width	47 mm
Plate hole length (Maximum)	46 mm
Plate hole width (Maximum)	35 mm
Plate hole diameter	6.7 mm

PRODUCT INFORMATION

COMPACTA

1430POI050P60-59X47 (24)

EAN 4031582332513



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

