

PRODUCT INFORMATION

BASETECH

POR080x30-Ø12 RAL9011 TFR

EAN 4031582414325



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Basetech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	100 kg
Electric Conductive	No
Stainless	No
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.06 kg

WHEEL

Body material	Polypropylene
Tread Material Mix	Identical with wheel body
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	80 mm
Tread width	30 mm
Axle Hole Diameter	20 mm
Hub Length	44 mm
Hardness of tread (D)	65 Shore D

BASETECH

POR080x30-Ø12 RAL9011 TFR

EAN 4031582414325



BETTER MOBILITY. BETTER LIFE.

Product Drawings

