PRODUCT INFORMATION

AGILA

2477PJO150R07-Ø19-21,5

EAN 4031582326550



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●○○
Attrition	●●●○○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Agila
Type	Swivel castor with total lock
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Electric Conductive	No
Stainless	No
Load capacity Static	200 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall Height	188 mm

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Broad
Swivel Bearing	Two ball races
Housing Color	Blue passivated
Offset	36 mm
Swivel radius	131 mm
Swivel interference	262 mm

WHEEL

Body material	Polypropylene
Tread Material Mix	Thermoplastic rubber
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	150 mm
Tread width	32 mm
Hardness of tread (A)	87 Shore A

FITTING

Fitting type	Synthetic expander, round
Expander fitting (Minimum)	19 mm
Expander fitting (Maximum)	21.5 mm
Hint	Please indicate required tube innerdiameter when ordering.

© Copyright 2026 TENTE International GmbH


AGILA


2477PJO150R07-Ø19-21,5

EAN 4031582326550

BETTER MOBILITY. BETTER LIFE.

Product Drawings





© Copyright 2026 TENTE International GmbH