

COMPACTA

1430POI032P60-38X32 (42)

EAN 4031582457872



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Compacta
Housing type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	20 kg
Load capacity Static	40 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	42.5 mm
Overall weight	0.046 kg

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	32 mm
Tread width	14 mm
Hardness of tread (D)	65 Shore D

HOUSING

Material fork	Steel sheet, light
Fork shape	Broad
Swivel bearing	One ball race
Offset	11 mm
Swivel radius	27 mm
Swivel interference	54 mm

FITTING

Fitting type	Rectangular plate
Plate length	38 mm
Plate width	32 mm
Plate hole length (Maximum)	30 mm
Plate hole width (Maximum)	24 mm
Plate hole diameter	4.2 mm

PRODUCT INFORMATION

COMPACTA

1430POI032P60-38X32 (42)

EAN 4031582457872



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

