

DELTA

3642ITP160P63 F.D-LOCK

EAN 4031582337426
Order number 00833691



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------------------------------|
| Product name | Delta |
| Type | Swivel castor with total lock, head end of castor |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 600 kg |
| Load capacity at 6 km/h | 480 kg |
| Load capacity Static | 1200 kg |
| Temperature range (Minimum) | -10 °C |
| Temperature range (Maximum) | 60 °C |
| Overall height | 210 mm |
| Overall width | 94 mm |
| Overall weight | 3.3 kg |

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Aluminium |
| Tread material | Polyurethane, casted |
| Bearing | Precision ball bearing |
| Axle | Screwed with nut |
| Wheel color | Honey yellow (RAL1005) |
| Threadguards | Without threadguard |
| Diameter | 160 mm |
| Tread width | 50 mm |
| Body width | 50 mm |
| Hardness of tread (A) | 92 Shore A |
| Hardness of tread (D) | 42 Shore D |

HOUSING

| | |
|---------------------|------------------------|
| Material fork | Steel sheet, heavy |
| Fork shape | Broad, reinforced |
| Swivel bearing | Precision ball bearing |
| Colour | Blue passivated |
| Offset | 55 mm |
| Swivel radius | 135 mm |
| Swivel interference | 270 mm |
| Dome diameter | 94 mm |

FITTING

| | |
|-----------------------------|--------------------------|
| Fitting type | Medium rectangular plate |
| Plate length | 137 mm |
| Plate width | 105 mm |
| Plate hole length (Minimum) | 75 mm |
| Plate hole length (Maximum) | 80 mm |
| Plate hole width (Minimum) | 105 mm |
| Plate hole width (Maximum) | 105 mm |
| Plate hole diameter | 11 mm |

DELTA

3642ITP160P63 F.D-LOCK

EAN 4031582337426
Order number 00833691



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

