

STORA

2370PJJ100P30-13 SYN.T/G

EAN 4031582365009
Order number 00033004



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Stora
Type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	176.37 lb
Load capacity Static	352.74 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	5.08 in
Overall width	2.36 in
Overall weight	1.18 lb

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Roller bearing
Wheel color	Silver gray (RAL7001)
Threadguards	With threadguard
Diameter	3.94 in
Tread width	1.26 in
Body width	1.26 in
Hardness of tread (A)	87 Shore A

HOUSING

Material	Steel sheet, medium
Fork shape	Slim
Swivel bearing	Two ball races
Color	Blue passivated
Offset	1.38 in
Swivel radius	3.35 in
Swivel interference	6.69 in
Dome diameter	2.36 in

FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.51 in

PRODUCT INFORMATION

STORA

2370PJJ100P30-13 SYN.T/G

EAN 4031582365009
Order number 00033004



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

