

# ALPHA

3477PVO125P30-13

EAN 4031582305616



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ● |
| Movement noise       | ● ● ● ● ● |
| Attrition            | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ● ● |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Alpha                         |
| Type                        | Swivel caster with total lock |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph    | 352.74 lb                     |
| Electric conductive         | no                            |
| Stainless                   | no                            |
| Load capacity Static        | 705.48 lb                     |
| Temperature range (Minimum) | -4 °F                         |
| Temperature range (Maximum) | 140 °F                        |
| Overall height              | 6.1 in                        |
| Overall weight              | 2.78 lb                       |

## HOUSING

|                     |                    |
|---------------------|--------------------|
| Housing Material    | Steel sheet, heavy |
| Fork shape          | Broad              |
| Swivel bearing      | Two ball races     |
| Housing Color       | Blue passivated    |
| Offset              | 1.57 in            |
| Swivel radius       | 4.76 in            |
| Swivel interference | 9.53 in            |

## WHEEL

|                       |                     |
|-----------------------|---------------------|
| Body material         | Polypropylene       |
| Tread material        | Solid rubber, black |
| Bearing               | Plain bearing       |
| Axle                  | Screwed with nut    |
| Threadguards          | Without threadguard |
| Diameter              | 4.92 in             |
| Tread width           | 1.46 in             |
| Hardness of tread (A) | 85 Shore A          |

## FITTING

|                    |           |
|--------------------|-----------|
| Fitting type       | Bolt hole |
| Bolt hole diameter | 0.51 in   |

# ALPHA

3477PVO125P30-13

EAN 4031582305616



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

