

ELASTECH

RK.XLR 125X40-Ø20 HL44 ESD

EAN 4031582508383
Order number 10011100



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Undefined
Tread material	Polypropylene, soft
Diameter	4.92 in
Tread width	1.57 in
Hardness of tread (A)	63 Shore A

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Elastech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	352.74 lb
Load capacity Static	705.48 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	176 °F
Overall weight	0.85 lb

ELASTECH

RK.XLR 125X40-Ø20 HL44 ESD

EAN 4031582508383
Order number 10011100



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

WB. XLR125x40-Ø20NL44 antistatic

