

# ELASTECH

RK.XLR 125X40-Ø20 HL44 ESD

EAN 4031582508383  
Order number 10011100



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Undefined
	soft
Tread material	Polypropylene, soft
Diameter	4.92 in
Tread width	1.57 in
Hardness of tread (A)	63 Shore A

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	352.74 lb
Load capacity Static	705.48 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	176 °F
Overall weight	0.85 lb

# ELASTECH

RK.XLR 125X40-Ø20 HL44 ESD

EAN 4031582508383  
Order number 10011100



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

WB. XLR125x40-Ø20NL44 antistatic

