

ELASTECH

UFR200X46-Ø25 TFR

EAN 4031582390674



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide
	soft
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	7.87 in
Tread width	1.81 in
Axle hole diameter	0.98 in
Hub length	2.28 in
Hardness of tread (A)	65 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	881.85 lb
Load capacity Static	1763.7 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	176 °F
Overall weight	2.49 lb

ELASTECH

UFR200X46-Ø25 TFR

EAN 4031582390674



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

