

COMPACTA

2198PII036P40-42

EAN 4031582332568



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Compacta
Housing type	Fixed castor
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	66.14 lb
Load capacity Static	132.28 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	122 °F
Overall height	1.89 in
Overall weight	0.13 lb

WHEEL

Body material	Polypropylene
Tread material	Solid rubber, non-marking
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	1.5 in
Tread width	0.59 in
Hardness of tread (A)	75 Shore A

HOUSING

Material	Steel sheet, medium
Fork shape	Angular
Swivel radius	1.26 in

FITTING

Fitting type	Square plate
Plate length	2.17 in
Plate width	0.98 in
Plate hole length (Maximum)	1.77 in
Plate hole width (Maximum)	1.77 in
Plate hole diameter	0.24 in

PRODUCT INFORMATION

COMPACTA

2198PII036P40-42

EAN 4031582332568



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

