

COMPACTA

2198PII036P40-42

EAN 4031582332568



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-----------------------------|
| Product name | Compacta |
| Type | Fixed castor |
| Standard | EN12528 - Furniture Castors |
| Load capacity at 1.8 mph | 66.14 lb |
| Load capacity Static | 132.28 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 122 °F |
| Overall height | 1.89 in |
| Overall weight | 0.13 lb |

WHEEL

| | |
|-----------------------|--------------------------------|
| Body material | Polypropylene |
| | soft |
| Tread material | Solid rubber, non-marking |
| Bearing | Plain bearing with spacer tube |
| Axle | Riveted |
| Threadguards | Without threadguard |
| Diameter | 1.5 in |
| Tread width | 0.59 in |
| Hardness of tread (A) | 75 Shore A |

HOUSING

| | |
|---------------|---------------------|
| Material | Steel sheet, medium |
| Fork shape | Angular |
| Swivel radius | 1.26 in |

FITTING

| | |
|-----------------------------|--------------|
| Fitting type | Square plate |
| Plate length | 2.17 in |
| Plate width | 0.98 in |
| Plate hole length (Maximum) | 1.77 in |
| Plate hole width (Maximum) | 1.77 in |
| Plate hole diameter | 0.24 in |

COMPACTA

2198PII036P40-42

EAN 4031582332568



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

