

AGILA

2470DIK125R47-32-35

EAN 4031582328394



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila
Housing type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	163 mm

WHEEL

Body material	Sheet Steel
Tread material	Solid rubber, non-marking
Bearing	Cone ball bearing
Threadguards	With threadguard
Diameter	125 mm
Tread width	32 mm
Hardness of tread (A)	80 Shore A

HOUSING

Material fork	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Offset	41 mm
Swivel radius	103.5 mm
Swivel interference	207 mm

FITTING

Fitting type	Synthetic expander, square
Expander fitting (Minimum)	32 mm
Expander fitting (Maximum)	35 mm
Hint	Please indicate required tube innerdiameter when ordering.

AGILA

2470DIK125R47-32-35

EAN 4031582328394



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

