

DURATECH

TOP 080X60-Ø25 HL60

EAN 4031582331011
Order number 00827802



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	80 mm
Tread width	60 mm
Axle hole diameter	25 mm
Hub length	60 mm
Body width	60 mm
Hardness of tread (D)	75 Shore D
Bearing type	6005

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	600 kg
Load capacity at 6 km/h	480 kg
Load capacity Static	1200 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	0.441 kg

DURATECH

TOP 080X60-Ø25 HL60

EAN 4031582331011
Order number 00827802



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

