

LUMINA

AA20PJ1050B10-11X22 TFR

EAN 4031582385823



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Lumina
Housing type	Swivel castor
Standard	EN12528 - Furniture Castors
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	2.46 in
Overall width	2.17 in
Overall weight	0.22 lb

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	1.97 in
Tread width	0.39 in
Hardness of tread (A)	87 Shore A

HOUSING

Material	Polypropylene
Fork shape	Twin wheel housing, closed
Swivel bearing	Stem, swiveling
Swivel radius	1.93 in
Swivel interference	3.86 in

FITTING

Fitting type	Stem with grip ring, with collar
Stem diameter	0.43 in