

# ALPHA

3478PJP200P63 65A

EAN 4031582416541  
Order number 00062374



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance ●●●○○

Movement noise ●●●●●

Attrition ●●●○○

Corrosion resistance ●●●○○

## CORE ATTRIBUTES

Product name	Alpha
Housing type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	250 kg
Load capacity Static	500 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	240 mm
Overall width	115 mm
Overall weight	1.775 kg

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Silver grey (RAL7001)
Threadguards	With threadguard
Diameter	200 mm
Tread width	46 mm
Body width	46 mm
Hardness of tread (A)	65 Shore A

## HOUSING

Material	Steel sheet, heavy
Fork shape	Broad
Colour	Blue passivated

## FITTING

Fitting type	Rectangular plate
Plate length	140 mm
Plate width	115 mm
Plate hole length (Minimum)	75 mm
Plate hole length (Maximum)	80 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	11 mm

# ALPHA

3478PJP200P63 65A

EAN 4031582416541  
Order number 00062374



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

