

NOVATECH

ITB125X50-Ø17 H7

EAN 4031582397888
Order number 00861396



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Aluminum
Tread material	Polyurethane, casted
Bearing	Bore with keyway
Threadguards	Without threadguard
Diameter	4.92 in
Tread width	1.97 in
Axle hole diameter	0.67 in
Hub length	2.13 in
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	1102.31 lb
Load capacity at 3.7 mph	881.85 lb
Load capacity Static	2204.62 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	1.75 lb

TECHNICAL DRAWINGS

