PRODUCT INFORMATION

KAPPA LOAD

9650TOP250P63 CL67

EAN 4031582314410

Image may differ from the original product

PERFORMANCE

Roll Performance	●●●●●
Movement noise	●●○○○
Attrition	●●●●●
Corrosion resistance	●●●●○

CORE ATTRIBUTES

Product name	Kappa load
Type	Swivel caster
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	2910.1 lb
Load capacity at 3.7 mph	2425.08 lb
Electric conductive	no
Stainless	no
Load capacity Static	4850.16 lb
Temperature range (Minimum)	-22 °F
Temperature range (Maximum)	176 °F
Overall height	12.01 in
Overall width	4.33 in
Overall weight	11.79 lb

HOUSING

Housing Material	Cast iron, or iron forged, heavy
Fork shape	Broad, reinforced
Swivel bearing	Deep-groove ball thrust roller bearing
Housing Color	Blue passivated
Offset	2.4 in
Swivel radius	7.38 in
Swivel interference	14.76 in
Lubrication nipple	1
Dome diameter	4.37 in

WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	9.84 in
Tread width	1.97 in
Body width	1.97 in
Hardness of tread (D)	75 Shore D

FITTING

Fitting type	Rectangular plate
Plate length	5.31 in
Plate width	4.33 in
Plate hole length (Minimum)	2.95 in
Plate hole length (Maximum)	3.15 in
Plate hole width (Minimum)	2.95 in
Plate hole width (Maximum)	4.13 in
Plate hole diameter	0.43 in

© Copyright 2026 TENTE International GmbH

KAPPA LOAD

9650TOP250P63 CL67

EAN 4031582314410

Order number 00830248

Product Drawings







© Copyright 2026 TENTE International GmbH