

PRODUCT INFORMATION

NOVATECH

FTF230x82-Ø45-5xØ14

EAN 4031582331974



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Electric conductive	no
Stainless	no
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	12.89 lb

WHEEL

Body material	Casting
Tread material	Polyurethane, casted
Bearing	Flanged wheel
Diameter	9.06 in
Tread width	3.23 in
Axle hole diameter	1.77 in
Hardness of tread (A)	92 Shore A
Hole circle diameter	2.76 in
Fitting hole diameter	0.55 in
Suitable for	jungheinrich_mic

FITTING

Bolt mounting holes quantity	5
------------------------------	---

