


NOVATECH

RK.ETP078x78-Ø47x16

EAN 4031582330069



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	700 kg
Nosivost na 6 km/h	840 kg
Električni provod	no
nerdjajuci	no
Statički Nosivost	1400 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0.67 kg

TOCAK

Materijal za telo	Nedefinisani
materijal omotaca	polipropilen, mekan
Prečnik	78 mm
Širina omotac	78 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D
Prečnik kuglicni lezaj	47 mm
Širina kuglicni lezaj	16 mm

