PRODUCT INFORMATION

AGILA

2478PJO075P60-67x60

EAN 4031582302387



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●●○
Attrition	●●●○○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Agila
Type	Fixed castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	75 kg
Electric Conductive	No
Stainless	No
Load capacity Static	150 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	100 mm
Overall width	43 mm
Overall weight	0.16 kg

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Broad
Housing Color	Blue passivated
Dome diameter	43 mm

WHEEL

Body material	Polypropylene
Tread Material Mix	Thermoplastic rubber
Bearing	Plain bearing
Wheel Color	Silver grey (RAL7001)
Threadguards	Without threadguard
Diameter	75 mm
Tread width	25 mm
Body width	25 mm
Hardness of tread (A)	87 Shore A

FITTING

Fitting type	Rectangular plate
Plate length	67 mm
Plate width	60 mm
Plate hole length (Minimum)	40 mm
Plate hole length (Maximum)	48 mm
Plate hole width (Minimum)	40 mm
Plate hole width (Maximum)	48 mm
Plate hole diameter	6.3 mm

© Copyright 2026 TENTE International GmbH


AGILA


2478PJO075P60-67x60

EAN 4031582302387

Order number 00003910

Product Drawings





© Copyright 2026 TENTE International GmbH