

NOVATECH

FTP 250X100-Ø35 HL120

EAN 4031582319361

Broj porudžbine 00801911



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Casting
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
stitnici omotaca	Sa threadguard
Prečnik	250 mm
Širina omotac	100 mm
dimenzija rupa osovina	35 mm
dužina glavcine	120 mm
Širina tela	100 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D

PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ● ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ● ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Standard	EN12533 - Tockovi za teske terete
Nosivost na 4 km/h	2640 kg
Nosivost na 6 km/h	2200 kg
Statički Nosivost	4400 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	15,059 kg

NOVATECH

FTP 250X100-Ø35 HL120

EAN 4031582319361
Broj porudžbine 00801911



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

