PRODUCT INFORMATION

# DURATECH

## TOP 250x50-Ø25 HL60

EAN 4031582322743



Image may differ from the original product

### PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●●● |
| Movement noise | ●●○○○ |
| Attrition | ●●●●● |
| Corrosion resistance | ●●●○○ |

### CORE ATTRIBUTES

| | |
|---|---|
| Product name | Duratech |
| Type | Wheel |
| Standard | EN12533 - Heavy Duty Castors |
| Load capacity at 2.5 mph | 2910.1 lb |
| Load capacity at 3.7 mph | 2425.08 lb |
| Electric conductive | no |
| Stainless | no |
| Load capacity Static | 4850.16 lb |
| Temperature range (Minimum) | -40 °F |
| Temperature range (Maximum) | 176 °F |
| Overall weight | 4.1 lb |

### WHEEL

| | |
|---|---|
| Body material | Polyamide, heavy |
| Tread material | Identical with wheel body |
| Bearing | Precision ball bearing |
| Wheel color | Natural white |
| Threadguards | Without threadguard |
| Diameter | 9.84 in |
| Tread width | 1.97 in |
| Axle hole diameter | 0.98 in |
| Hub length | 2.36 in |
| Body width | 1.97 in |
| Hardness of tread (D) | 75 Shore D |
| Bearing type | 6205 |

© Copyright 2026 TENTE International GmbH


# DURATECH

## TOP 250x50-Ø25 HL60

EAN 4031582322743

Order number 00801309

**Product Drawings**





© Copyright 2026 TENTE International GmbH

# DURATECH

## TOP 250x50-Ø25-HL60

EAN 4031582322743

Order number 0080L409




© Copyright 2026 TENTE International GmbH