

DURATECH HEAT

W00075X25-Ø8 HL26,5

EAN 4031582367355



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Thermoplastic synthetics, heat resistant
Tread material	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	2.95 in
Tread width	0.98 in
Axle hole diameter	0.31 in
Hub length	1.04 in

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech heat
Housing type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	165.35 lb
Load capacity Static	330.69 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	392 °F

DURATECH HEAT

W00075X25-Ø8 HL26,5

EAN 4031582367355



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

